

□□□ □□□□□ □□□ □□ □□ □□□

□□:

- □ □□□ □□ □□ □ □□□, 6 □□ □ 4 □□, □□□□ □□□ □□ □□.
- □□, □□ □□□ □□□, □□ □□.
- □□ □□□□□□.
- □□□ □□, □□ □□ □□□ □□, □ □□□, □□ □□.
- SpO2 □□, PR, □□ □ □ PI.
- □□□□ □□□ □□□ □□□ □□□□ (□□ □□□ □□ □□□ □□□ **OEM**)

□□□:

SpO2	
□□ □□:	35 ~ 100 %
□□:	1%
□□□:	80 % ~ 100 % (□ 2 %) □ 70 % ~ 80 % (□ 3 %) □ □□□ (≤70 %)
□□ □□ :	50 % -100 %
□□□	
□□ □□	30-250BPM
□□	1BPM
□□□	2BPM
PI	
□□	0 ~ 30 %
□□	0.1 %
□□□	□ 1 %
□□□	CEFDA



□□□□□□□□□□ [factory](#)

FINGERTIP PULSE OXIMETER

- SIMPLE OPERATION
- DISPLAY FAST
- EASY TO CARRY
- HIGH ACCURACY

□□ □□ □□

□□ (L × W × H)	57mm × 31mm × 31mm
□□□	55g
□□ □□ □□ (L × W × H)	80mm × 60mm × 38mm
□□ □□ □□ (L × W × H)	430mm × 340mm × 200mm
□□□ (100pcs)	6□□□□
□□	□□

□ □□□□:

Shipping service



□□ : □□ **TT** □□□ **100 %**

□□ : □□□ □□ □□□ □□□□□

□□ □□□□ **60** □□□□.

NaNNaNNaNNaN